



Spotting Tables

Professional COLD and STEAM spotting tables which are ideal to remove any kind of stain in both the dry-cleaning and garment industries.



Technical data	JOLLY	JOLLY S
Required power	230/1 or 400V/3+N- 50Hz	230/1 or 400V/3+N- 50Hz
Vacuum motor	0,25 kW	0,25 kW
Compressor motor	2,2 kW	-
Air inlet	1/4"	1/4 "
Air consumption	150 ÷ 200 Nl/min	150 ÷ 200 NI/min
Air working pressure	7 ÷ 8 Bar	7 ÷ 8 Bar
Steam inlet	3/8"	1/2 "
Return outlet	1/2 "	1/2 "
Steam consumption	3 ÷ 5 kg/h	6 ÷ 8 kg/h
Steam working pressure	4 ÷ 6 bar	4 ÷ 6 bar
Vacuum outlet	ø100 mm	ø100 mm
Encumbrance	1440 x 700 mm	1440 x 700 mm
Net weight	60 kg	65 kg
Gross weight	80 kg	85 kg
Overall dimensions	1380 x 580 x 1070 mm	1380 x 580 x 1070 mm
Volume	0,85 m³	0,85 m³

*other voltages by request. For manufacturing necessities the above-mentioned specifications are not binding



Features:

- Stainless steel board and sleeve spotting arm.
- Garment tray.
- · Cooling coil.
- Air filter.
- Two spotting guns and two tanks for liquid spotting agents.
- Air drying gun.
- Available with built-in vacuum unit or ready for connection to central vacuum supply.

Available extras:

- Suction cap either ready for external exhaust or with activated carbons filter
- Built-in compressor
- Steam and air gun assembly.



Features:

- Stainless steel board and sleeve spotting arm.
- Steam available in three different options: dry, wet and a mix of steam and water.
- Vacuum is concentrated on both the nose of the board and the swinging sleeve shape and combined with the heated compressed air from the gun it quickens the drying phase and keeps moistened areas from spreading.
- Ready for connection to central vacuum (or with built-in vacuum by request).

Available extras:

- Built-in vacuum unit
- Water spray gun with condenser
- Cold spotting gun with tank for spotting agents.



Q +44 (020) 8579 2661



mail@renzacci.co.uk



www.renzacci.co.uk